

POSTPRINTING EQUIPMENT



FT AIR B2



Forno a passaggio con doppio tappeto



Pass-through dryer with double carpet






FT AIR B2 è un forno elettrico a tappeto per l'asciugatura di piccole dimensioni realizzato in carpenteria medio – leggera e montato su ruote per un facile spostamento.

Il tunnel coibentato è riscaldato a mezzo di resistenze elettriche con termoventilazione canalizzata per una rapida essiccazione e un riciclo d' aria calda in camera per abbattere i consumi.

B2 è provvisto di Pannello Touch per l'impostazione della temperatura del forno e della velocità del tappeto.

L'apertura regolabile su entrambi i lati consente di ridurre la fuoriuscita di calore, contribuendo ad abbattere i consumi del forno.



Specifiche tecniche

Larghezza Tunnel: da 650 a 1200mm

Lunghezza Tunnel: 2200mm

Altezza utile tunnel: 100mm

Temperatura massima: 180°C

Alimentazione: 400-230V 16 Kw

Velocità tappeto e temperatura regolabili da pannello



B2 is an electric dryer with conveyor belt made of medium - light carpentry and mounted on wheels for easy movement.

The insulated tunnel is heated by means of electric resistances with ducted fan ventilation for rapid drying and a hot air recirculation in the tunnel to reduce consumption.

B2 is provided with a user friendly control touch panel for setting the oven temperature and the belt speed.

The adjustable opening on both sides allows to reduce heat loss, helping to reduce the consumption of the oven.



Technical Specifications

Tunnel width: from 650 to 1200mm

Tunnel lenght: 2200mm

Usable tunnel height: 100mm

Max. temperature: 180°C

Power supply: 400-230V 16 Kw

Belt speed and temperature adjustable from panel



Ser.Tec. Srl

Via Emilio Salgari 14/d - 31056 Roncade (TV) - Italy
Phone +39 (0)422 798184 - Fax. +39 (0)422 799711
e-mail: sales@ser-tec.org - Website: ser-tec.org



www.facebook.com/sertecsr1



www.instagram.com/sertecgroup

Ser.Tec. reserves the right to make changes in specifications, materials and accessories without notice.

The result may differ from the information in this brochure.



**Scan the QR code and
watch the video of
B2**